



## Small details, **big impact**

Epredia Benchtop Appliances

Find it at [fisherhealthcare.com](https://fisherhealthcare.com)



# Epredia Slimline Wax Dispenser



- Ultra-fast heating system with digital temperature controls, minimizes the wait for molten wax
- Insulated aluminum tank provides good thermal conductivity and improved temperature control
- Non-drip, three-position lever tap – push dispense, lock open for rapid delivery or locked closed for safety
- Dedicated tap heating system and integrated filter screen (0.5 mm mesh) prevent blockages and ensures even flow of wax
- High tap position (153 mm from the bench) accommodates large containers for transferring molten wax
- Anti-microbial coating (Ag+) to inhibit growth of bacteria.

## Epredia Slimline Wax Dispenser

Epredia Slimline Wax Dispenser 230V **A84600001**

Epredia Slimline Wax Dispenser 110V **A84600002**

Country of origin: United Kingdom

Capacity: 7.5 L (6 kg of pelletized wax)

Dimensions: 420.5 x 181 x 435.5 mm (D x W x H)

Temperature range: Ambient – 70 °C (±1 °C) at 25 °C

Power supply: 110V ac 50/60 Hz or 230 V ac 50/60 Hz

Rating: 480 Watts

Weight: 7 kg (15.4 lbs)

Power cable: USA, UK / EU (Schuko)



With fast delivery of molten wax, the dispenser is a perfect complement to the Epredia™ HistoStar™ Embedding Center

# Epredia Paratrimmer

The Epredia™ Paratrimmer™ paraffin block trimmer enables efficient removal of excess wax from the outside of cassettes with no risk of damage to printed text or barcodes and with improved safety for staff.

- Ultra-fast heating system with variable temperature control and memory function to retain desired start up temperature
- Built-in waste wax collection system
- Large heated work surface allows users to de-wax multiple blocks at once
- Anti-microbial paint finish (silver ion) to inhibit growth of bacteria

## Epredia Paratrimmer

Epredia Paratrimmer 230V **A84600080**

Epredia Paratrimmer 110V **A84600081**

Country of origin: United Kingdom

Dimensions: 202 x 152 X 183.5 mm (D x W x H)

Temperature range: Ambient – 85 °C (±1 °C) at 25 °C

Power supply: 110 V ac 50/60 Hz or 230 V ac 50/60 Hz

Rating: 250 Watts

Weight: 3.0 Kg (5 lbs)

Power cable: USA, UK / EU (Schuko)





## Epredia Slimline Hotplate

Optimize your laboratory's slide mounting workflow with Epredia hotplates. Designed for quick drying of slides and easy repositioning of paraffin samples, each features an ultra-fast heating system and small form factor.

- Matte black heating surface coating for optimal visual contrast for paraffin tissue sections
- Ultra-fast heating system with variable temperature control and memory function that retains desired start-up temperature
- Optional stainless steel lid for improved heating efficiency
- Moveable slide support rails
- Bright LED display for temperature control
- Anti-microbial coating

### Epredia Slimline Hotplate

Epredia Slimline Hotplate 230V	A84600030
Epredia Slimline Hotplate 110V	A84600031
Epredia Slimline Hotplate Lid	A84610081
Country of origin: United Kingdom	
Dimensions: 450 x 183 x 85.5 mm (D x W x H)	
Temperature Range: Ambient – 95 °C (±1 °C) at 20 °C	
Power Supply: 110 V ac 50/60 Hz or 230 V ac 50/60 Hz	
Rating: 400 Watts	
Weight: 2.2 Kg (4.4 lbs)	
Power Cable: USA, UK / EU (Schuko)	

## Epredia Digital Tissue Section Bath

The Epredia Digital Tissue Section Bath features innovative digital controls that maintain water temperature, allowing tissue sections to be efficiently flattened prior to being lifted onto a microscope slide. It has an extra-deep bowl (85mm) for easy section pick up, allowing slides to be fully dipped at any angle, without hitting the bottom.

- Ultra-fast heating system
- Significant slide drying area at the rear of the instrument
- A secure-fitting lid (optional) reduces airborne contamination, evaporation and improves heating efficiency
- Automatic over-temperature cut-out for safety
- Anti-microbial paint finish

### Epredia Tissue Section Bath

Epredia Tissue Section Bath 230V	A84600060
Epredia Tissue Section Bath 110V	A84600061
Epredia Tissue Section Bath Lid	A84610141
Country of origin: United Kingdom	
Bowl Capacity: 3.5L	
Dimensions: 370 x 295 x 135 mm (D x W x H)	
Temperature Range: Ambient – 30 - 70 °C (±1 °C) at 45 °C	
Power Supply: 110V ac 50/60 Hz or 230 V ac 50/60 Hz	
Rating: 400 Watts	
Weight: 4.5 Kg (10 lbs)	
Power Cable: USA, UK / EU (Schuko)	



# Epredia High-Capacity Section Dryer

Our section dryers offer rapid, efficient drying of sections without overheating the specimen. They draw air through the bottom of the unit and circulate it at a digitally controlled temperature.

- 390 slide capacity – 13 racks of 30 slides including the rack hanger and handle.
- Ultra-fast heating system for rapid warm up.
- Digital temperature control accurate to  $\pm 1\text{ }^{\circ}\text{C}$  at  $45^{\circ}\text{C}$ .
- Fan assisted heating – sections dry in approximately 10 minutes.
- Controls are located on top of instruments to protect from moisture.
- Innovative resistance hinges - allow the door to be positioned at any angle
- Anti-microbial finish

## Epredia High-Capacity Section Dryer

Epredia High-Capacity Section Dryer 230V	A84600050
Epredia High-Capacity Section Dryer 110V	A84600051
High-Capacity Section Dryer Four-Rack Timer Unit B	A84610121
High-Capacity Section Dryer Four-Rack Timer Unit C	A84610122
Country of origin: United Kingdom	
Dimensions: 320 x 469 x 346 mm (D x W x H)	
Temperature Range: Ambient – $75\text{ }^{\circ}\text{C}$ ( $\pm 1\text{ }^{\circ}\text{C}$ ) at $45\text{ }^{\circ}\text{C}$	
Power Supply: 110 V ac 50/60 Hz or 230 V ac 50/60 Hz	
Rating: 1,000 Watts	
Weight: 15.4 Kg (33.8 lbs)	
Power Cable: USA or UK / EU (Schuko)	



Optional timers for the High-Capacity Section Dryer

# Ordering Information

Product	Cat. No.
<b>Epredia Slimline Wax Dispenser</b>	
Epredia Slimline Wax Dispenser 230V	A84600001
Epredia Slimline Wax Dispenser 110V	A84600002
<b>Epredia Slimline Hotplate</b>	
Epredia Slimline Hotplate 230V	A84600030
Epredia Slimline Hotplate 110V	A84600031
Slimline Hotplate Lid	A84610081
<b>Epredia High-Capacity Section Dryer</b>	
Epredia High-Capacity Section Dryer 230V	A84600050
Epredia High-Capacity Section Dryer 110V	A84600051
High-Capacity Section Dryer Four-Rack Timer Unit B	A84610121
High-Capacity Section Dryer Four-Rack Timer Unit C	A84610122
<b>Epredia Paratrimmer</b>	
Epredia Paratrimmer 230V	A84600080
Epredia Paratrimmer 110V	A84600081
<b>Epredia Digital Tissue Section Bath</b>	
Epredia Digital Tissue Section Bath 230V	A84600060
Epredia Digital Tissue Section Bath 110V	A84600061
Digital Tissue Section Bath Lid	A84610141

Distributed by Fisher Healthcare

Contact us today:

#### In the United States

Order online: [fisherhealthcare.com](http://fisherhealthcare.com)

Fax an order: 1-800-290-0290

Call customer service: 1-800-640-0640

© 2022 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at [fishersci.com/trademarks](http://fishersci.com/trademarks).

BN20225239

