



Slide clarity – **pure and simple**

When conducting immunohistochemistry (IHC) assays, it can be frustrating when pretreated slides come out murky. Incomplete dewaxing can make it feel like you're looking through a dirty window, and can interfere with diagnostics, decrease laboratory efficiency, and drive up operating costs.

Dewax and HIER buffers by Epredia achieve all-in-one epitope retrieval and deparaffinization in the PT Module ahead of IHC. Dewax and HIER buffers demonstrate superior dewaxing performance over other PTM buffers. Unlike other processes, slides are not recoated with molten paraffin, resulting in enhanced clarity in imaging.

Dewax and HIER buffers are color-coded into three pH groups, allowing you to easily differentiate between tanks. All Dewax and HIER buffers come pre-measured for ease of use in the PT Module.

For more information on achieving better clarity in your immunohistochemical assays, please contact your local Epredia representative today.



Find it at fisherhealthcare.com

 **fisher**
healthcare
part of Thermo Fisher Scientific

**Dewax and HIER buffers
come in three pH ranges:**



Dewax and HIER buffer L is a low pH (~6) buffer and is citrate-based (orange coloration).



Dewax and HIER buffer M is a mid pH (~8) buffer and is EDTA-based (purple coloration).




Dewax and HIER buffer H is a high pH (~9) buffer and is Tris-EDTA-based (blue coloration).

**Clarity doesn't have
to come at a big cost.**

Epredia Dewax and HIER Buffers deliver high quality at a competitive cost per slide. Get a clearer picture of how you may be able to save 40% or more per test. Contact your Epredia representative today.

See the difference for yourself.
Contact your Epredia representative today and ask about Dewax and HIER buffers.

Item	Use	REF Num
Dewax and HIER buffer (H, M, L) variety pack	IVD	TA-999-DHBVP
Dewax and HIER buffer H (15x concentrate) 10 x 100 mL	IVD	TA-999-DHBH
Dewax and HIER buffer L (15x concentrate) 10 x 100 mL	IVD	TA-999-DHBL
Dewax and HIER buffer M (15x concentrate) 10 x 100 mL	IVD	TA-999-DHBM



Distributed by Fisher Healthcare
Contact us today:

In the United States

Order online: fisherhealthcare.com
Fax an order: 1-800-290-0290
Call customer service: 1-800-640-0640

