

NEW

Thermo Scientific Heratherm large capacity microbiological incubators – safe, easy, efficient

Thermo Scientific™ Heratherm® large capacity microbiological incubators are the right choice for large samples or high sample volume.

General Protocol units with gravity convection minimize drying out of samples. Advanced Protocol Security models with mechanical convection technology provide outstanding temperature performance to ensure fully reproducible results.

750 L | 400 L



safe, easy, efficient



Safety

- Optimal temperature performance to protect your valuable samples
- Automatic overtemperature alarm
- Safe view of samples through internal glass door without impact on temperature

Ease of use

- Easy temperature setting with intuitive user interface
- Large vacuum fluorescent display for easy reading
- Simple calibration routine

Optional stainless steel exterior for Advanced Protocol Security units

- Meets demanding needs in pharmaceutical and clinical laboratories

Heratherm

General Protocol Incubators

- Two sizes (400 L and 750 L)
- Gravity convection technology with unique airflow has been developed to minimize drying out of samples
- Optimal use of chamber with flexible shelving system and lockable castors for easy set-up / moving

Heratherm

Advanced Protocol Security Incubators

- Mechanical convection technology ensures optimal temperature distribution with improved level of temperature uniformity: ± 0.2 to 0.3 °C
- Temperature range from ambient $+5$ °C to 105 °C for application flexibility: units can even be used for drying applications
- Unique 140 °C decontamination cycle, eliminating the need for separate autoclaving or use of toxic decontaminants

LARGE CAPACITY GENERAL PROTOCOL INCUBATORS*

GRAVITY CONVECTION

ORDER NUMBER	MODEL	INTERNAL VOLUME L/CU.FT.	MAXIMUM TEMPERATURE °C
51029321	IGS400	405 / 14.3	75
51029333	IGS750	747 / 26.4	75

* All units are 120V

** Stainless steel exterior

LARGE CAPACITY ADVANCED PROTOCOL SECURITY INCUBATORS*

MECHANICAL CONVECTION

ORDER NUMBER	MODEL	INTERNAL VOLUME L/CU.FT.	MAXIMUM TEMPERATURE °C
51029323	IMH400-S	381 / 13.4	105
51029324	IMH400-S SS**	381 / 13.4	105
51029335	IMH750-S	702 / 24.8	105
51029336	IMH750-S SS**	702 / 24.8	105

ORDER TODAY

[Name] at
[Phone] or
[eMail@eMail.com]

© 2012 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.



In the United States:
For customer service, call 1-800-766-7000.
To fax an order, use 1-800-926-1166.
To order online: www.fishersci.com
©2011 Thermo Fisher Scientific Inc. All rights reserved.

In Canada:
For customer service, call 1-800-234-7437.
To fax an order, use 1-800-463-2996.
To order online: www.fishersci.ca



Part of Thermo Fisher Scientific