thermo scientific

Act Now! Special package offers.* Shake up the world of science

Choose the ideal shaker package for your proteomic and genomic application needs and receive a platform and clamps to provide maximized capacity



Thermo Scientific[™] MaxQ[™] Digital Shakers

- A digital shaker designed to provide reliable results required for bacteria and yeast cultures
- Durable triple eccentric drive backed by 10 year parts warranty
- Maximize capacity of 250mL and 2L flasks in a compact footprint
- · Digital display with simultaneous viewing of temperature, speed and time with audible and visual alarms



Thermo Scientific MaxQ Digital High Performance Shakers

- A digital high performance shaker designed for large or heavy loads to maximize your production
- Increased weight capacity of 71lbs for heavy loading
- Doubled capacity of 250mL and 2L flasks for high throughput shaking
- Options available for continuous or timed runs for added flexibility

Each package includes shaker, platform and clamps in one part number for easy ordering



Proteomic Packages

Packages designed to be reliable, simple-to-use and flexible for protein expression.

- Choose from three shaker configuration options: benchtop, stackable, or large stackable
- Each shaker has package configurations optimized for 250mL or 2L flasks to maximize your research
- Incubated units are designed to maintain 37°C which is ideal for bacteria and yeast
- Refrigerated units are designed to hold temperatures at 4°C or 15°C below ambient which is ideal for protein expression

	Application Package	Shaker Description	Accessories Description	Pkg Qty	Promo Part Number	
	Benchtop Package A	MaxQ 4000 with refrigeration	18x18" universal platform	1	11676170	
			250mL flask clamps	16		
	Benchtop Package B		18x18" universal platform	1	11676171	
			2L flask clamps	6		
	Stackable Package A	MaxQ 6000 with refrigeration	18x18" universal platform	1	11676172	
			2L flask clamps	6		
	Stackable Package B		18x18" universal platform	1	11676173	
			250mL flask clamps	16		
	Large Stackable Package A	MaxQ 8000 with refrigeration	29.5x18" universal platform	1	11676174	
			250mL flask clamps	30		
	Large Stackable Package B		29.5x18" universal platform	1	11070175	
			2L flask clamps	12	11676175	



thermo scientific





Genomic Packages

Select a package ideally suited to protect your valuable samples by delivering outstanding performance, accuracy and reproducible results.

- Each shaker has package configurations optimized for 250mL or 1L flasks to maximize your research
- Incubated shaker packages are available in temperatures up to 80°C
- Open air shaker packages are available in a variety of sizes or capacities to fit your lab's needs

	Application Package	Shaker Model	Shaker Description	Accessories Description	Pkg Qty	Promo Part Number
	Small Open Air		Digital Shaker	18x18" universal platform	1	- 11676176
	Package A	- MaxQ 2000		250mL flask clamps	16	
	Small Open Air Package B			18x18" universal platform	1	- 11676177
				1L flask clamps	9	
	Mid-Sized Open Air Package A	— MaxQ HP416	High Performance Digital Shaker	250/300mL dedicated platform with 35 pre-installed clamps	1	11676178
	Mid-Sized Open Air Package B			1L dedicated platform with 12 pre-installed clamps	1	11676179
	Large Open Air Package A	— Max0 HP430	High Performance Digital Shaker	250/300mL dedicated platform with 70 pre-installed clamps	1	11676182
	Large Open Air Package B	— MaxQ HP430		1L dedicated platform with 24 pre-installed clamps	1	11676183
	Small Incubated Package A		Digital Shaker	13x11" universal platform	1	- 11676180
		- MaxQ 4450		1L flask clamps	4	
	Small Incubated Package B			13x11" universal platform	1	- 11676181
				250mL flask clamps	9	
	Large Incubated Package A	— Max0 HP420	High Performance Digital Shaker	250/300mL dedicated platform with 25 pre-installed clamps	1	11676184
	Large Incubated Package B	— iviaxų HP420		1L dedicated platform with 8 pre-installed clamps	1	11676185

*Valid in the United States (excluding Puerto Rico) and Canada while supplies last for orders received between January 1, 2018 and June 30, 2018 and in connection with the products listed above. Not valid in connection with any other promotion or discount. Offer void where prohibited, licensed or restricted by federal, state, provincial, or local laws or regulation or agency/institutional policy. Other restrictions may apply. Customer acknowledges that this offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by customer in accordance with all federal and state laws, including without limitation the federal anti-kickback law (42 C.F.R. § 1320a-7b(b)(3)(A)) and regulations thereunder (42 C.F.R. §1001.952(h)).

Find out more at fishersci.com/promotions

In the United States:

For customer service, call 1-800-766-7000 To fax an order, use 1-800-926-1166 To order online: fishersci.com

In Canada:

For customer service, call 1-800-234-7437 To fax an order, use 1-800-463-2996 To order online: fishersci.ca



© 2018 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. **BN0321165**