

# Isotemp\* Refrigerators and Freezers

## Flammable Material Laboratory Refrigerators and Freezers

### Fisher Scientific\* Isotemp Flammable Material Laboratory Refrigerators and Freezers

*Designed to store volatiles where a spark-free internal cabinet environment is required*

Isotemp flammable material refrigerators, freezers and combination units are designed to be used for storage of volatiles where a spark-free internal cabinet environment is required. A range of models particularly suited for storage of flammable materials with sizes from small undercounter to full height freestanding. Not available outside North America.

- » Spark-free interiors to reduce risk of internal explosion
- » All units are manual defrost
- » Tough white exterior (except Cat. No. 13-986-450R)
- » CFC- and HCFC-free refrigeration system and insulation
- » Designed to meet NFPA 45 and 99 along with OSHA article 1910.307

Warranty: 13 months parts and labor  
CSA and/or UL listed



97-925-1

13-986-450R

13-986-152

13-986-111A

Capacity	Style	Interior D x W x H	Exterior L x W x H	Temperature Range	Defrost	No. of Shelves	Electrical Requirements; Plug Type	Weight (Shipping)	Cat. No.
<b>Refrigerators</b>									
5.6 cu. ft.	Undercounter	16 x 20 x 27.5"	28.75 x 23.5 x 33.5"	1° to 12°C	Manual	4 adjustable	120V 60Hz; NEMA 5-15	110 lb.	<b>97-938-1</b>
21.0 cu. ft.	Upright	16.5 x 27 x 55"	31.75 x 32 x 74.5"	1° to 12°C	Manual	4 fixed	115V 60Hz; NEMA 5-15	230 lb.	<b>13-986-152</b>
50.0 cu. ft.	Upright, double-door	26.5 x 45.75 x 59"	34.25 x 52 x 77.25"	1° to 12°C	Manual	8 adjustable	115V 60Hz; NEMA 5-15	400 lb.	<b>13-986-450R</b>
<b>Freezers</b>									
5.0 cu. ft.	Undercounter	15 x 18 x 28.5"	31.4 x 21 x 33.5"	-12° to -20°C	Manual	2 fixed, 3 door	115V 60Hz; NEMA 5-15	84 lb.	<b>97-925-1</b>
20.6 cu. ft.	Upright	20 x 27 x 57"	36 x 72 x 73"	-12° to -20°C	Manual	4 fixed	115V 60Hz; NEMA 5-15	200 lb.	<b>13-986-149</b>
<b>Combination Refrigerator/Freezer</b>									
5.6 cu. ft.	Undercounter	Ref: 18 x 15 x 21" Frz: 11 x 15 x 5"	25.5 x 21.25 x 32.75"	Ref: 1° to 12°C Frz: -12° to -20°C	Manual	Ref: 3 fixed, 3 door	120V 60Hz; NEMA 5-15	78 lb.	<b>97-935-1</b>
10.0 cu. ft.	Upright	Ref: 13.5 x 19.5 x 38.5" Frz: 15 x 17.5 x 11.5"	30 x 23.5 x 60"	Ref: 1° to 12°C Frz: -12° to -20°C	Manual	Ref: 4 door, 3 adjustable; Frz: 1 fixed	120V 60Hz; NEMA 5-15	150 lb.	<b>13-986-111A</b>



**Fisher Scientific**

Part of Thermo Fisher Scientific

For customer service, call 1-800-766-7000.  
To fax an order, use 1-800-926-1166.  
To order online: [www.fishersci.com](http://www.fishersci.com)

©2011 Thermo Fisher Scientific Inc. All rights reserved.

\*All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.