

The 2024 Wildcat Collection of Fisher Scientific Products

Your Prime Supplier for All Your Laboratory Needs

Get competitive pricing, standard shipping at no cost, next-day shipping on in-stock items, and product samples with the Wildcat Collection.* These products are conveniently listed on iBuyNU under the Fisher Scientific Punchout – find the collection in the “My List” dropdown tab or search for “Wildcat.”

PPE

Description	Cat. No.	Quantity
Gloves		
Fisherbrand™ Powder Free Nitrile Gloves, Blue, Sizes Small to X-Large	19-190-1597B, C, D, E	1000/Case
Hourglass International™ HandPRO™ RoyalTouch300™ Nitrile Exam Gloves, Blue, Sizes X-Small to X-Large	18-041-140, 18-041-141, 18-041-142, 18-041-143, 18-041-144	3000/Case
Kimberly-Clark Professional™ Kimtech™ Purple Nitrile™ Gloves, Sizes X-Small to X-Large	19-149-863A, 19-149-863B, 19-149-863C, 19-149-863D	1000/Case
Ansell MICROFLEX™ 92-134 Nitrile Glove Nitrile Gloves, Sizes Small to X-Large	17-000-312, 17-000-313, 17-000-314, 17-000-315	1000/Case
Miscellaneous Fisherbrand PPE		
Clear Safety Glasses, Wraparound	19-181-514	Each
Safety Goggles, Clear Frames	12-888-304	Each
Safety Goggles, Gray Frames	19-181-513	Each
Class A First Aid Kit	19-090-860	Each
Disposable Isolation Gowns	12-893-005	100/Case
Non-Skid Shoe Covers	12-896-0022	1000/Case

Lab Essentials

Description	Cat. No.	Quantity
Fisherbrand Laboratory Notebooks		
Black, 100 pages	FB14127557	Each
Black, 200 pages	FB14127558	Each
Blue, 100 pages	FB14127561	Each
Blue, 200 pages	FB14127562	Each
Miscellaneous Fisherbrand Essentials		
Lab Mat, Silicone, 35 x 60 cm	14-127-555	Each
Task Wipers, Small (4.5 x 8.5 in.)	06-666A	280/Pack
Fisherbrand Premium Microcentrifuge Tubes		
0.6 mL, Natural	05-408-120	5000/Case
1.5 mL, Natural	05-408-129	5000/Case
2 mL, Natural	05-408-138	5000/Case
Fisherbrand™ Easy Reader™ Centrifuge Tubes		
15 mL, Racks	05-539-12	500/Case
15 mL, Sleeves	07-200-886	500/Case
50 mL, Racks	05-539-8	500/Case
50 mL, Bulk	05-539-13	500/Case

Lab Essentials (continued)

Description	Cat. No.	Quantity
Fisherbrand PCR Tubes		
Tubes, 0.2 mL, Flat Cap	14-230-225	1000/Case
Tube Strips, 0.2 mL Flat Cap	14-230-215	1000/Case
Fisherbrand Cryogenic Storage Tubes		
Vials, 2 mL, External Threads	10-500-26	100/Pack
Vials, 2 mL, Internal Threads	12-567-501	100/Pack
Fisherbrand Pipets		
Pasteur Pipets, Disposable, L: 5.75 in.	13-678-20A	720/Case
Pasteur Pipets, Disposable, L: 9 in.	13-678-20C	720/Case
Transfer Pipets, Disposable, 5.8 mL	13-711-9AM	500/Pack
Fisherbrand Cryogenic/Freezer Boxes (5 x 5 x 2 in.)		
Fiberboard, 81 Places	03-395-464	Each
Fiberboard, 100 Places	03-395-465	Each
Fiberboard, Hinged Lid, 81 Places, White	13-131-000	Each
Fiberboard, Hinged Lid, 81 Places, Blue	13-131-001	Each
Fiberboard, Hinged Lid, 81 Places, Green	13-131-002	Each
Fiberboard, Hinged Lid, 81 Places, Purple	13-131-003	Each
Fisherbrand Freeze Cubes		
Freeze Cube XL, with Cooling Block, Capacity: 30 x 1 to 2 mL Vials	13-131-006	Each
Freeze Cube XL, with Cooling Block, Capacity: 96 x 0.2 mL PCR Tubes	13-131-009	Each
Fisherbrand General Purpose Syringes		
Sterile, Polypropylene, Luer Lock, 1 mL	14-955-464	100/Pack
Sterile, Polypropylene, Luer Lock, 3 mL	14-955-457	100/Pack
Sterile, Polypropylene, Luer Lock, 5 mL	14-955-458	100/Pack
Sterile, Polypropylene, Luer Lock, 10 mL	14-955-459	100/Pack
Sterile, Polypropylene, Luer Lock, 20 mL	14-955-460	50/Pack
Sterile, Polypropylene, Luer Lock, 60 mL	14-955-461	50/Pack

Some products may have limited availability.

Cell Culture

Description	Cat. No.	Quantity
Fisherbrand Serological Pipets		
1 mL	13-678-11B	1000 Case
2 mL	13-678-11C	500/Case
5 mL	13-678-11D	200/Case
10 mL	13-678-11E	200/Case
25 mL	13-67-811	200/Case
50 mL	13-678-11F	100/Case

Fisher Scientific Sales Representatives

Mike Gorack (312) 350-7520 mike.gorack@thermofisher.com
Jorge Rendon (224) 277-3858 jorge.rendon@thermofisher.com

Cell Culture (continued)

Description	Cat. No.	Quantity
Fisherbrand Tissue Culture Flasks		
T25, Vented Cap, 50 mL	FB012935	200/Case
T25, Plug Seal Cap, 50 mL	FB012936	200/Case
T75, Vented Cap, 250 mL	FB012937	100/Case
T75, Plug Seal Cap, 250 mL	FB012938	100/Case
T182, Vented Cap, 600 mL	FB012939	40/Case
T182, Plug Seal Cap, 600 mL	FB012940	40/Case
Thermo Scientific™ BioLite Cell Culture Treated Flasks		
T25, 50 mL, Vented	12-556-009	200/Case
T25, 50 mL, Plug Seal	12-556-012	100/Case
T75, 250 mL, Vented	12-556-010	40/Case
T75, 250 mL, Plug Seal	12-556-013	200/Case
T182, 600 mL, Vented	12-556-011	100/Case
T182, 600 mL, Plug Seal	12-556-014	40/Case
Fisherbrand Tissue Culture Dishes (Dia. x H)		
35 x 12 mm	FB012920	960/Case
60 x 18 mm	FB012921	600/Case
70 x 15 mm	FB012922	600/Case
90 x 17 mm	FB012923	500/Case
100 x 22 mm	FB012924	300/Case
150 x 22 mm	FB012925	120/Case
Thermo Scientific BioLite Cell Culture Treated Dishes (Dia. x H)		
35 x 10 mm	12-556-000	500/Case
60 x 15 mm	12-556-001	500/Case
100 x 20 mm	12-556-002	200/Case
150 x 20 mm	12-556-003	120/Case
Fisherbrand Tissue Culture Plates		
6 Wells, 17 mL	FB012927	100/Case
12 Wells, 6.8 mL	FB012928	100/Case
24 Wells, 3.5 mL	FB012929	100/Case
48 Wells, 1.55 mL	FB012930	100/Case
96 Wells, 0.3 mL	FB012931	100/Case
Thermo Scientific BioLite Multidishes and Microwell Plates		
6 Wells, 3 mL	12-556-004	50/Case
12 Wells, 2 mL	12-556-005	50/Case
24 Wells, 1 mL	01-549-765	50/Case
48 Wells, 0.5 mL	12-556-007	50/Case
96 Wells, 0.2 mL	12-556-008	50/Case
Fisherbrand Bottle Top Filters		
Filter Unit with Bottle, PES Membrane, 0.2 µm, 250 mL	FB12566502	12/Case
Filter Unit with Bottle, PES Membrane, 0.45 µm, 250 mL	FB12566503	12/Case
Filter Unit with Bottle, PES Membrane, 0.2 µm, 500 mL	FB12566504	12/Case
Filter Unit with Bottle, PES Membrane, 0.45 µm, 500 mL	FB12566505	12/Case
Fisherbrand Sterile Cell Strainers		
Cell Strainer, White, 70 µm	22-363-548	50/Case
Cell Strainer, Yellow, 100 µm	22-363-549	50/Case
Cell Strainer, Blue, 40 µm	22-363-547	50/Case

Pipette Tips

Description	Cat. No.	Quantity
Fisherbrand™ SureOne™ Pipette Tips		
10 µL, Micropoint, HR*	02-707-436	960/Pack
10 µL, Micropoint, Sterile, HR*	02-707-437	960/Pack
10 µL, Extended Length, Sterile, HR*	02-707-441	960/Pack
200 µL, Micropoint, HR*	02-707-424	960/Pack
200 µL, Micropoint, Sterile, HR*	02-707-425	960/Pack
200 µL Micropoint, RD**	02-707-426	960/Pack
200 µL, Beveled Tip, HR*	02-707-418	960/Pack
200 µL, Beveled Tip, RD**	02-707-420	960/Pack

Pipette Tips (continued)

Description	Cat. No.	Quantity
Fisherbrand™ SureOne™ Pipette Tips		
300 µL, Sterile, HR*	02-707-410	960/Pack
300 µL, RD**	02-707-411	960/Pack
1000 µL, HR*	02-707-401	960/Pack
1000 µL, Sterile, HR*	02-707-402	960/Pack
Fisherbrand SureOne Filter Pipette Tips		
10 µL, Filtered, Sterile, HR*	02-707-439	960/Pack
10 µL, Extended Length, Filtered, Sterile, HR*	02-707-442	960/Pack
20 µL, Filtered, Sterile, HR*	02-707-432	960/Pack
100 µL, Filtered, Sterile, HR*	02-707-431	960/Pack
100 µL, Filtered, Sterile, RD**	02-707-477	960/Pack
200 µL, Filtered, Sterile, HR*	02-707-430	960/Pack
300 µL, Filtered, Sterile, HR*	02-707-471	960/Pack
1000 µL, Filtered, Sterile, HR*	02-707-404	960/Pack
1000 µL, Extended Length, Filtered, Sterile	13-811-164	768/Pack

*Hinged Rack

**Reload

Solvents

Description	Cat. No.	Quantity
Fisher Bioreagents™ Products		
EDTA, Electrophoresis Grade	BP120500	500 g
DMSO	BP231100	100 mL
Glycerol, Molecular Biology Grade	BP2291	1 L
PBS, 10X	BP3991	1 L
Sodium Chloride	BP3581	1 kg
SDS, Electrophoresis Grade	BP166500	500 g
Tris Base	BP154-1	1 kg
Agar	BP1423500	500 g
Agarose, Molecular Biology Grade	BP160500	500 g
Water, DNase- and RNase-Free	BP2484100	100 mL
Fisher BioReagents™ Tween™ 20	BP337100	100 mL
D-Sucrose, Molecular Biology Grade	BP2201	1 kg
Yeast Extract	BP1422500	500 g
Glycine	BP3811	1 kg
Formamide, Molecular Biology Grade	BP227500	500 mL
Fisher Chemical™ Solvents		
2-Propanol, Certified ACS	A41620	20 L
2-Propanol, Certified ACS	A4164	4 L, 4 x 4 L
Acetone, Certified ACS	A1820	20 L
Acetone, Certified ACS	A184	4 L, 4 x 4 L
Acetone, HPLC	A9494	4 L, 4 x 4 L
Acetonitrile, HPLC, Safe-Cote™ Bottles	A998SK4	4 L, 4 x 4 L
Acetonitrile, Optima Grade	A9964	4 L, 4 x 4 L
Alcohol Reagent, Poly Bottles	A962P4	4 L, 4 x 4 L
Ethanol, Anhydrous (Histological)	A405P4	4 L, 4 x 4 L
Ethyl Acetate, Certified ACS/HPLC	E1954	4 L, 4 x 4 L
Ethyl Acetate, Certified ACS	E14520	20 L
Ethyl Ether Anhydrous	E1384	4 L, 4 x 4 L
Ethyl Ether, Anhydrous, BHT, Certified ACS	E13820	20 L
Hexanes, ACS, Metal Can	H29220	20 L
Hexanes, ACS	H2924	4 L, 4 x 4 L
Methanol, Certified ACS/HPLC	A4524	4 L, 4 x 4 L
Methanol, Certified ACS	A41220	20 L
Methanol, LC/MS, Optima	A4564	4 L, 4 x 4 L
Methylene Chloride, Certified ACS	D3720	20 L
Methylene Chloride, Certified ACS	D374	4 L, 4 x 4 L
Methylene Chloride, Certified ACS/HPLC	D1434	4 L, 4 x 4 L
N,N-Dimethylformamide, Certified ACS	D1194	4 L, 4 x 4 L
Tetrahydrofuran, HPLC	T4254	4 L, 4 x 4 L
Water, LC/MS, Optima	W64	4 L, 4 x 4 L

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: [fishersci.com](#)

Call customer service: 1-800-766-7000

In Canada

Order online: [fishersci.ca](#)

Call customer service: 1-800-234-7437

