



The 2018 Wildcat Collection of Fisher Scientific Products

Your Prime Supplier for All Your Laboratory Needs

Get competitive pricing, standard shipping at no cost, next-day delivery and product samples with the Wildcat Collection, available in the Fisher Scientific™ stockroom.

The Wildcat Collection is conveniently listed on iBuyNU under the Fisher Scientific Punchout – find it in the “My List” dropdown tab or search for “wildcat.”

Safety Supplies

| Description | Cat. No. | Quantity |
|--|---|------------|
| Fisherbrand™ Personal Protective Equipment | | |
| Gloves | | |
| Comfort Nitrile Exam Gloves, Blue, 3mil, Sizes X-Small to X-Large | 19-041-171A, B, C, D, E | 2,000/Case |
| Powder-Free Nitrile Exam Gloves, Blue, 4mil, Sizes X-Small to 2X-Large | 19-130-1597A, B, C, D, E, F | 1,000/Case |
| Powder-Free Nitrile Gloves, Black, 4mil, Sizes X-Small to 2X-Large | 19-156-300, 19-181-603, 4, 5, 6, 7 | 1,000/Case |
| Powder-Free Nitrile Gloves, Purple, 4mil, Sizes Small to X-Large | 19-181-608, 9, 10, 11 | 1,000/Case |
| Miscellaneous Fisherbrand PPE | | |
| Clear Safety Glasses, Wraparound | 19-181-514 | 12/Pack |
| Safety Goggles, Clear Frames | 19-181-512 | 12/Pack |
| Safety Goggles, Gray Frames | 19-181-513 | 12/Pack |
| Class A First Aid Kit | 19-090-860 | 1 Each |
| Lab Coats | See NU ORS | |

Lab Essentials

| Description | Cat. No. | Quantity |
|--|-------------------|------------|
| Fisherbrand Laboratory Notebooks | | |
| Black, 100 pages | FB14127557 | 1 Each |
| Black, 200 pages | FB14127558 | 1 Each |
| Blue, 100 pages | FB14127561 | 1 Each |
| Blue, 200 pages | FB14127562 | 1 Each |
| Miscellaneous Fisherbrand Essentials | | |
| Lab Mat, Silicone, 35 x 60cm | 14-127-555 | 1 Each |
| Task Wipers, Small (4.5 x 8.5 in.) | 06666A | 280/Pack |
| Fisherbrand Premium Microcentrifuge Tubes | | |
| 0.6mL, Natural | 05-408-120 | 5,000/Case |
| 1.5mL, Natural | 05-408-129 | 5,000/Case |
| 2mL, Natural | 05-408-138 | 5,000/Case |

Lab Essentials (continued)

| Description | Cat. No. | Quantity |
|--|-------------------|------------|
| Fisherbrand™ Easy Reader™ Centrifuge Tubes | | |
| 15mL, Racks | 05-539-12 | 500/Case |
| 15mL, Sleeves | 07-200-886 | 500/Case |
| 50mL, Sleeves | 06-443-19 | 500/Case |
| 50mL, Racks | 06-443-18 | 500/Case |
| Fisherbrand PCR Tubes | | |
| Tubes, 0.2mL, Flat Cap | 14-230-225 | 1,000/Case |
| Tube Strips, 0.2mL, Flat Cap | 14-230-215 | 1,000/Case |
| Fisherbrand Cryogenic Storage Tubes | | |
| Vials, 2mL, External Threads | 10-500-26 | 100/Pack |
| Vials, 2mL, Internal Threads | 12-567-501 | 100/Pack |
| Fisherbrand Pipets | | |
| Pasteur Pipets, Disposable, L: 5.75 in. | 13-678-20A | 720/Case |
| Pasteur Pipets, Disposable, L: 9 in. | 13-678-20C | 720/Case |
| Transfer Pipets, Disposable, 7.5mL | 13-711-9D | 500/Case |
| Fisherbrand Cryogenic/Freezer Storage Boxes | | |
| Fiberboard, 81 Places, 5 x 5 x 2 in. | 03-395-464 | 1 Each |
| Fiberboard, 100 Places, 5 x 5 x 2 in. | 03-395-465 | 1 Each |
| Fiberboard, Hinged Lid, 81 Places, 5 x 5 x 2 in. | 13-131-000 | 1 Each |
| Fisherbrand Freeze Cubes | | |
| Freeze Cube XL, with Cooling Block, Capacity: 30 x 1-2mL Vials | 13-131-006 | 1 Each |
| Freeze Cube XL, with Cooling Block, Capacity: 96 x 0.2mL PCR Tubes | 13-131-009 | 1 Each |
| Fisherbrand General Purpose Syringes | | |
| Sterile, PP, Luer Lock, 1mL | 14-955-456 | 100/Pack |
| Sterile, PP, Luer Lock, 3mL | 14-955-457 | 100/Pack |
| Sterile, PP, Luer Lock, 5mL | 14-955-458 | 100/Pack |
| Sterile, PP, Luer Lock, 10mL | 14-955-459 | 100/Pack |
| Sterile, PP, Luer Lock, 20mL | 14-955-460 | 50/Pack |
| Sterile, PP, Luer Lock, 60mL | 14-955-461 | 50/Pack |

Fisher Scientific Sales Representatives

| | | |
|--------------------------|----------------|------------------------------------|
| Jarod Schweighart | (773) 531-6290 | jarod.schweighart@thermofisher.com |
| Mike Gorack | (312) 350-7520 | mike.gorack@thermofisher.com |
| Laura Thurman | (312) 898-0803 | laura.thurman@thermofisher.com |



Cell Culture

| Description | Cat. No. | Quantity |
|---|-------------------|------------|
| Fisherbrand Serological Pipets | | |
| Capacity: 1mL | 13-678-11B | 1,000/Case |
| Capacity: 2mL | 13-678-11C | 500/Case |
| Capacity: 5mL | 13-678-11D | 200/Case |
| Capacity: 10mL | 13-678-11E | 200/Case |
| Capacity: 25mL | 13-67-811 | 200/Case |
| Capacity: 50mL | 13-678-11F | 100/Case |
| Fisherbrand Tissue Culture Flasks | | |
| T25, Vented Cap, 50mL | FB012935 | 200/Case |
| T25, Plug Seal Cap, 50mL | FB012936 | 200/Case |
| T75, Vented Cap, 250mL | FB012937 | 100/Case |
| T75, Plug Seal Cap, 250mL | FB012938 | 100/Case |
| T182, Vented Cap, 600mL | FB012939 | 40/Case |
| T182, Plug Seal Cap, 600mL | FB012940 | 40/Case |
| Fisherbrand Tissue Culture Dishes | | |
| Dia. x H: 35 x 12mm | FB012920 | 960/Case |
| Dia. x H: 60 x 18mm | FB012921 | 600/Case |
| Dia. x H: 70 x 15mm | FB012922 | 600/Case |
| Dia. x H: 90 x 17mm | FB012923 | 500/Case |
| Dia. x H: 100 x 22mm | FB012924 | 300/Case |
| Dia. x H: 150 x 22mm | FB012925 | 120/Case |
| Fisherbrand Tissue Culture Plates | | |
| Wells: 6 x 17mL, Flat Bottomed | FB012927 | 100/Case |
| Wells: 12 x 6.8mL, Flat Bottomed | FB012928 | 100/Case |
| Wells: 24 x 3.5mL, Flat Bottomed | FB012929 | 100/Case |
| Wells: 48 x 1.55mL, Flat Bottomed | FB012930 | 100/Case |
| Well: 96 x 0.3mL, Flat Bottomed | FB012931 | 100/Case |
| Fisherbrand Bottle Top Filters | | |
| Filter Unit w/Bottle, PES Mem., 0.2µm, 250mL | FB12566502 | 12/Case |
| Filter Unit w/Bottle, PES Mem., 0.45µm, 250mL | FB12566503 | 12/Case |
| Filter Unit w/Bottle, PES Mem., 0.2µm, 500mL | FB12566504 | 12/Case |
| Filter Unit w/Bottle, PES Mem., 0.45µm, 500mL | FB12566505 | 12/Case |

Pipette Tips

| Description | Cat. No. | Quantity |
|---|-------------------|----------|
| Fisherbrand™ SureOne™ Pipette Tips | | |
| 10µL, Micropoint, Sterile, HR* | 02-707-437 | 960/Pack |
| 10µL, Micropoint, RD* | 02-707-438 | 960/Pack |
| 10µL, Extended Length, Sterile, HR* | 02-707-441 | 960/Pack |
| 10µL, Extended Length, Sterile, RD* | 02-707-442 | 960/Pack |
| 10µL, Extended Length, Filtered, Sterile, HR* | 02-707-444 | 960/Pack |
| 10µL, Extended Length, Filtered, Sterile, RD* | 02-707-474 | 960/Pack |
| 200µL, Micropoint, HR* | 02-707-424 | 960/Pack |
| 200µL, Micropoint, Sterile, HR* | 02-707-425 | 960/Pack |
| 200µL, Micropoint, RD* | 02-707-426 | 960/Pack |
| 200µL, Beveled Tip, HR* | 02-707-418 | 960/Pack |
| 200µL, Beveled Tip, RD* | 02-707-420 | 960/Pack |
| 300µL, Sterile, HR* | 02-707-410 | 960/Pack |
| 300µL, RD* | 02-707-411 | 960/Pack |
| 1000µL, HR* | 02-707-402 | 960/Pack |
| 1000µL, RD* | 02-707-403 | 960/Pack |
| 1000µL, Extended Length, HR* | 13-811-167 | 768/Pack |
| 1000µL, Extended Length, RD* | 13-811-166 | 768/Pack |

*HR=Hinged Rack, RD=Reload

iBuy **NU**



In the United States:

For customer service, call 1-800-766-7000
 To fax an order, use 1-800-926-1166
 To order online: fishersci.com

© 2018 Thermo Fisher Scientific Inc. All rights reserved.
 Trademarks used are owned as indicated at fishersci.com/trademarks.

Pipette Tips (continued)

| Description | Cat. No. | Quantity |
|--|-------------------|----------|
| Fisherbrand SureOne Filter Pipette Tips | | |
| 10µL, Filtered, Sterile, HR* | 02-707-439 | 960/Pack |
| 10µL, Filtered, Sterile, RD* | 02-707-473 | 960/Pack |
| 10µL, Extended Length, Filtered, Sterile, HR* | 02-707-442 | 960/Pack |
| 10µL, Extended Length, Filtered, Sterile, RD* | 02-707-474 | 960/Pack |
| 20µL, Filtered, Sterile, HR* | 02-707-432 | 960/Pack |
| 100µL, Filtered, Sterile, HR* | 02-707-431 | 960/Pack |
| 100µL, Filtered, Sterile, RD* | 02-707-477 | 960/Pack |
| 200µL, Filtered, Sterile, HR* | 02-707-430 | 960/Pack |
| 200µL, Filtered, Sterile, RD* | 02-707-478 | 960/Pack |
| 300µL, Filtered, Sterile, HR* | 02-707-471 | 960/Pack |
| 1000µL, Filtered, Sterile, HR* | 02-707-404 | 960/Pack |
| 1000µL, Filtered, Sterile, RD* | 02-707-480 | 560/Pack |
| 1000µL, Extended Length, Filtered, Sterile | 13-811-164 | 768/Pack |

*HR=Hinged Rack, RD=Reload

Solvents

| Description | Cat. No. | Quantity |
|--|------------------|------------|
| Fisher BioReagents™ Products | | |
| EDTA, Electrophoresis Grade | BP120500 | 1 x 500g |
| DMSO | BP231100 | 1 x 100mL |
| Glycerol, Molecular Biology Grade | BP2291 | 1 x 1L |
| PBS, 10X | BP3991 | 1 x 1L |
| Sodium Chloride | BP3581 | 1 x 1kg |
| SDS, Electrophoresis Grade | BP166500 | 1 x 500g |
| TRIS BASE | BP152-1 | 1 x 1kg |
| Agar | BP1423500 | 1 x 500g |
| Agarose, Molecular Biology Grade | BP160500 | 1 x 500g |
| Water, DNase- and RNase-Free | BP2484100 | 1 x 100mL |
| Fisher BioReagents™ Tween™ 20 | BP337100 | 1 x 100mL |
| D-Sucrose, Molecular Biology Grade | BP2201 | 1 x 1kg |
| Yeast Extract | BP1422500 | 1 x 500g |
| Glycine | BP3811 | 1 x 1kg |
| Formamide, Molecular Biology Grade | BP227500 | 1 x 500mL |
| Fisher Chemical™ Solvents | | |
| 2-Propanol, Certified ACS | A41620 | 20L |
| 2-Propanol, Certified ACS | A4164 | 1x4L, 4x4L |
| Acetone, Certified ACS | A1820 | 20L |
| Acetone, Certified ACS | A184 | 1x4L, 4x4L |
| Acetone, HPLC | A9494 | 1x4L, 4x4L |
| Acetonitrile, HPLC, Safe-Cote™ Bottles | A998SK4 | 1x4L, 4x4L |
| Acetonitrile, Fisher Chemical™ Optima™ Grade | A9964 | 1x4L, 4x4L |
| Alcohol Reagent, Poly Bottles | A962P4 | 1x4L, 4x4L |
| Ethanol, Anhydrous (Histological) | A405P4 | 1x4L, 4x4L |
| Ethyl Acetate, Certified ACS/HPLC | E1954 | 1x4L, 4x4L |
| Ethyl Acetate, Certified ACS | E14520 | 20L |
| Ethyl Ether Anhydrous | E1384 | 1x4L, 4x4L |
| Ethyl Ether, Anhydrous, BHT, Certified ACS | E13820 | 20L |
| Hexanes, ACS, Metal Can | H29220 | 20L |
| Hexanes, ACS | H2924 | 1x4L, 4x4L |
| Methanol, Certified ACS/HPLC | A4524 | 1x4L, 4x4L |
| Methanol, Certified ACS | A41220 | 20L |
| Methanol, LC/MS, Optima | A4564 | 1x4L, 4x4L |
| Methylene Chloride, Certified ACS | D3720 | 20L |
| Methylene Chloride, Certified ACS | D374 | 1x4L, 4x4L |
| Methylene Chloride, Certified ACS/HPLC | D1434 | 1x4L, 4x4L |
| N,N-Dimethylformamide, Certified ACS | D1194 | 1x4L, 4x4L |
| Tetrahydrofuran, HPLC | T4254 | 1x4L, 4x4L |
| Water, LC/MS, Optima | W64 | 1x4L, 4x4L |

fisher scientific
 part of Thermo Fisher Scientific