

Simplify your selection process with the OHAUS guide to centrifuge and rotor bundles! Featuring combinations designed around specific centrifugation applications, from high speed to cell culture to microplate, OHAUS has the right centrifuge and rotor packages to help you **Do More** in your laboratory.

High-Speed Micro – Non-Refrigerated Bundles



FC5515

| Type | Max. Tube Qty | Volume | RPM | RCF | Bundle Contents | Item No | Rotor |
|----------------|---------------|------------|--------|--------|-----------------------|----------|-------|
| Standard | 24 | 1.5/2.0 mL | 15,200 | 21,953 | Centrifuge FC5515 | 30130867 | |
| | | | | | Rotor 24 x 1.5/2.0 mL | 30130870 | |
| Biocontainment | 30 | 1.5/2.0 mL | 13,500 | 19,150 | Centrifuge FC5515 | 30130867 | |
| | | | | | Rotor 30 x 1.5/2.0 mL | 30130872 | |
| High Volume | 44 | 1.5/2.0 mL | 15,000 | 21,379 | Centrifuge FC5515 | 30130867 | |
| | | | | | Rotor 44 x 1.5/2.0 mL | 30372717 | |

High-Speed Micro – Refrigerated Bundles




FC5515R

| Type | Max. Tube Qty | Volume | RPM | RCF | Bundle Contents | Item No | Rotor |
|----------------|---------------|------------|--------|--------|-----------------------|----------|-------|
| Standard | 24 | 1.5/2.0 mL | 15,200 | 21,953 | Centrifuge FC5515R | 30130869 | |
| | | | | | Rotor 24 x 1.5/2.0 mL | 30130870 | |
| Biocontainment | 30 | 1.5/2.0 mL | 13,500 | 19,150 | Centrifuge FC5515R | 30130869 | |
| | | | | | Rotor 30 x 1.5/2.0 mL | 30130872 | |
| High Volume | 44 | 1.5/2.0 mL | 15,000 | 21,379 | Centrifuge FC5515R | 30130869 | |
| | | | | | Rotor 44 x 1.5/2.0 mL | 30372717 | |

Low Volume – Cell Culture Bundles



FC5706

| Type | Max. Tube Qty | Volume | RPM | RCF | Bundle Contents | Item No | Rotor |
|------------------|---------------|------------|-------|-------|------------------------------|----------|---|
| Non-Refrigerated | 6 | 15 or 50mL | 6,000 | 4,427 | Centrifuge FC5706 | 30130876 |  |
| | | | | | Rotor 6 x 50 mL | 30130878 | |
| | | | | | Adapters (qty 3) 15 mL Tubes | 30130893 | |



Mid Volume – Cell Culture Bundles



FC5718R



FC5718

| Type | Max. Tube Qty | Volume | RPM | RCF | Bundle Contents | Item No | Rotor |
|------------------|-----------------------|-------------|-------|-------|-------------------------|----------|---|
| Refrigerated | 6 x 15 mL 4 x 50mL | 15 and 50mL | 5,000 | 3,885 | Centrifuge FC5718R | 30314815 |  |
| | | | | | Rotor 4 x 100 mL | 30314823 | |
| | | | | | Adapter Bucket, 3x15 mL | 30314882 | |
| | | | | | Adapter Bucket, 2x50ml | 30314881 | |
| Non-Refrigerated | 6 x 15 mL 4 x 50mL | 15 and 50mL | 5,000 | 3,885 | Centrifuge FC5718 | 30314813 |  |
| | | | | | Rotor 4 x 100 mL | 30314823 | |
| | | | | | Adapter Bucket, 3x15 mL | 30314882 | |
| | | | | | Adapter Bucket, 2x50ml | 30314881 | |

High Volume – Cell Culture Bundles



FC5816R



FC5816

| Type | Max. Tube Qty | Volume | RPM | RCF | Bundle Contents | Item No | Rotor |
|------------------|-------------------------|--------------|-------|-------|-----------------------|----------|-------|
| Refrigerated | 14 x 15 mL 6 x 50 mL | 15 and 50 mL | 4,500 | 3,780 | Centrifuge FC5816R | 30314819 | |
| | | | | | Rotor 4 x 250 mL | 30314820 | |
| | | | | | Adapter Rack, 7x15 mL | 30314913 | |
| | | | | | Adapter Rack, 3x50 mL | 30314906 | |
| Non-Refrigerated | 14 x 15 mL 6 x 50 mL | 15 and 50 mL | 4,500 | 3,780 | Centrifuge FC5816 | 30314817 | |
| | | | | | Rotor 4 x 250 ml | 30314820 | |
| | | | | | Adapter Rack, 7x15 mL | 30314913 | |
| | | | | | Adapter Rack, 3x50 mL | 30314906 | |

Microplate Bundles



FC5714



FC5714R

| Type | Max. Tube Qty | Volume | RPM | RCF | Bundle Contents | Item No | Rotor |
|------------------|-----------------------|-------------------|-------|-------|-------------------|----------|-------|
| Non-Refrigerated | 6 x Microtiter plates | Microtiter plates | 4,500 | 2,716 | Centrifuge FC5714 | 30314811 | |
| | | | | | Rotor 2 x 3MTP | 30314824 | |
| Refrigerated | 6 x Microtiter plates | Microtiter plates | 4,500 | 2,716 | Centrifuge FC5714 | 30314815 | |
| | | | | | Rotor 2 x 3MTP | 30314824 | |