

Spill Control and Containment

Find essentials that offer reliable protection from hazardous spills in your healthcare facility — all backed by industry-experienced safety specialists.



Safety

Protecting What Matters Most

Absorbents

Choose from a variety of absorbent pads, pillows, sacks, socs, and rolls that help contain fluid leaks and spills.



Granular Absorbents

Product Description	Packaging	Quantity	Cat. No.
Brady™ SPC™ Absorbents SpillFix Granular for Hydrocarbons, Water-Based Fluids, and Most Aggressive Chemicals, 100% Recycled Material, Biodegradable	3 qt.	6/Case	19-666-506
	7 lb. Bag	128/Pack	19-666-505
	20 lb. Bag	48/Pack	19-666-504

Universal Absorbents

For oil, water-based, and chemical liquid spills.



Product Description	Capacity	Dimensions	Quantity	Cat. No.
Brady™ Allwik™ Pillows for Tight Spaces, Gray	14 gal. (53 L)	18 x 18 in. (46 x 46 cm)	8/Case	17-111-167
	26 gal. (98 L)		16/Case	19-000-166
	15.4 gal. (58 L)	9 x 9 in. (23 x 23 cm)	32/Case	19-049-154
Brady™ MRO Plus™ Pads, Medium Weight, Gray	26 gal. (98 L)	19 x 15 in. (48.2 x 38 cm)	100/Case	19-000-162
Brady™ MRO Plus™ Pads, Heavyweight, Gray	20.5 gal. (77.6 L)	19 x 15 in. (48.2 x 38 cm)	100/Case	19-000-163
Fisherbrand™ All-Purpose Universal Absorbent Pads, Lightweight, Gray	44 gal. (166.5 L)	19 x 15 in. (48.2 x 38 cm)	200/Case	19-140-910
Fisherbrand™ All-Purpose Universal Absorbent Pads, Medium Weight, Gray	25 gal. (94.6 L)	19 x 15 in. (48.2 x 38 cm)	100/Case	19-140-911

Spill Control and Containment

Safety

Protecting What Matters Most

Universal Absorbents (cont.)

For oil, water-based, and chemical liquid spills.



Product Description	Capacity	Dimensions	Quantity	Cat. No.
Fisherbrand™ All-Purpose Universal Absorbent Rolls, Heavyweight, Gray	38 gal. (144 L)	30 in. x 150 ft. (96 cm x 46 m)	Each	19-140-913
Vileda Professional™ SpillEx Absorbent Floor Pads, Polymer, Polyethylene, White	Water: 1200 mL, NaCl 0.9%: Up to 500 mL	20 x 15 in. (50 cm x 38 cm)	10/Pack, 100/Case	19-200-790
	Water: 1200 mL, NaCl 0.9%: Up to 500 mL	20 x 15 in. (50 cm x 38 cm)	200/Case	19-200-719
	Water: 1200 mL, NaCl 0.9%: Up to 500 mL	20 x 15 in. (50 cm x 38 cm)	50/Case	19-200-791

Chemical Absorbents



Product Description	Capacity	Dimensions	Quantity	Cat. No.
Brady™ BRIGHTSORB™ Heavyweight Chemical Absorbent Pads for Continuous Leaks and Larger Spills, Yellow (Black/Red Print)	22 gal. (83.3 L)	19 x 15 in. (48.2 x 38 cm)	100/Case	19-150-260
Brady™ BRIGHTSORB™ Lightweight Chemical Absorbent Pads for Smaller Leaks and Drips, Yellow (Black/Red Print)	28 gal. (106 L)	19 x 15 in. (48.2 x 38 cm)	200/Case	19-103-101
Brady™ BrightSorb™ High Visibility Pillows for Chemicals, Acids, and Bases, Surfactant-Treated Polypropylene (Black/Red on Yellow)	14 gal. (52.99 L)	18 x 18 in. (20.32 cm x 20.32 cm)	16/Case	19-000-677
Brady™ BrightSorb™ High Visibility SOCs, for Chemicals, Acids, and Bases Including Hydrofluoric Acid (Black/Red on Yellow)	12 gal. (45.42 L)	12 ft. x 3 in. (3.65 m x 7.62 cm)	4/Case	19-000-676
	12 gal. (45.42 L)	4 ft. x 3 in. (1.21 m x 7.62 cm)	12/Case	19-000-678
Brady™ SPC Hazwik Sorbent Socs for Hydrofluoric Acid and Other Chemical Spills, Green	12 gal. (45 L)	3 in. x 12 ft. (7.6 cm x 3.65 m)	4/Case	19-819-443
Fisherbrand™ Chemical Absorbent Pads, Heavyweight, Yellow	22 gal. (83 L)	19 x 15 in. (48.2 x 38 cm)	100/Pack	19-140-918

Spill Control and Containment

Safety

Protecting What Matters Most



Spill Kits

Product Description	Capacity	Quantity	Cat. No.
General Purpose Spill Kits			
Brady™ Allwik™ Emergency Spill Saks for Overspray Leaks and Drips, Black Drawstring Bag Contains Pads, Socs, Pillow, Disposal Bag, Gloves, and Instructions	10 gal.	Each	17-111-278
Brady™ Universal Economy Spill Kits for Water-Based, Petroleum-Based, Non-Aggressive Chemical Fluids, High-Visibility Yellow Tote Contains Pads, Socs, Gloves, Disposal Bag, Instructions	5 gal. (19 L)	Each	17-111-228
Chemical Spill Kits			
Brady™ SPC Hazwik Economy Spill Kits for Hydro-Fluoric Acid and Other Chemical Spills, Includes Pads, Socs, Gloves, Disposal Bag, Instructions	5 gal. (19 L)	Each	19-150-268
Brady™ SPC Hazwik Emergency Response Spill Kits for Hydrofluoric Acid and Other Chemical Spills, Includes Pads, Socs, Pillow, Gloves, Goggles, Disposal Bags, Instructions	15 gal. (57 L)	Each	19-150-272
Biological Fluids Spill Kits			
New Pig Blood, Vomit & Urine Spill Kits, Single Use	2.9 gal. (11 L)	10/Case	19-041-554

Spill Control and Containment

Safety

Protecting What Matters Most

Spill Containment

Find cans, trays, and berms that enable containment of spills and safe clean-up and disposal of hazardous liquid and chemicals.



Disposal Cans and Basins

Product Description	Capacity	Dimensions	Quantity	Cat. No.
Justrite™ Fuel/Chemical Disposal Cans with Quick-Disconnect Faucets, Tubing Diameter: 0.25 in.	5 gal. (19 L)	H x Dia.: 20 x 12 in. (51 x 31 cm)	Each	19-413-824
Justrite™ Fuel/Chemical Disposal Cans with Quick-Disconnect Faucets, Tubing Diameter: 0.375 in.	5 gal. (19 L)	H x Dia.: 20 x 12 in. (51 x 31 cm)	Each	19-413-824
Justrite™ Disposal Can Spill Basins, Leakproof, Translucent, Durable PE, Holds Cans Up to 12 in. (30.5 cm) Diameter	5 gal. (19 L)	15 x 15 x 7.6 in. (38 x 38 x 19 cm)	Each	19-413-824

Spill Trays and Berms



Product Description	Capacity	Dimensions (L x W x H)	Quantity	Cat. No.
Justrite™ EcoPolyBlend™ Spill Trays, 100% Recycled PE, Black	12 gal. (45 L)	46 x 16 x 5.5 in. (117 x 41 x 14 cm)	Each	19-075-350
	20 gal. (75 L)	38 x 26 x 5.5 in. (96.5 x 66 x 14 cm)	Each	19-075-351
	23 gal. (87 L)	38 x 34 x 5.5 in. (96.5 x 86 x 14 cm)	Each	19-075-353
Justrite™ Mini-Berm Flex Spill Control Trays, Modified PVC-Coated Black Fabric, Foldable, Rigid Corner Supports, Sturdy Foam Walls, 1 in. NPT Drain Fitting, Utility Strap	30 gal. (113.5 L)	3 ft. x 3 ft. x 6 in. (91 x 91 x 15 cm)	Each	19-111-028
	55 gal. (208 L)	4 ft. x 4 ft. x 6 in. (122 x 122 x 15 cm)	Each	19-111-029
	70 gal. (265 L)	5 ft. x 4 ft. x 6 in. (152 x 122 x 15 cm)	Each	19-111-030
	110 gal. (416 L)	6 ft. x 5 ft. x 6 in. (183 x 154 x 15 cm)	Each	19-111-031
Justrite™ Maintenance Spill Berms, PVC-Coated Yellow Fabric (UV and Chemical Resistant), Encased Urethane Foam Sidewalls, Brass Corner Grommets	10 gal. (38 L)	2 ft. x 2 ft. x 4 in. (61 x 61 x 10 cm)	Each	19-111-014
	20 gal. (76 L)	2 ft x 4 ft x 4 in. (122 x 61 x 10 cm)	Each	19-111-015
	5 gal. (19 L)	2 ft. x 2 ft. x 4 in. (61 x 61 x 5 cm)	Each	19-111-021
	10 gal. (38 L)	2 ft. x 4 ft. x 4 in. (122 x 61 x 5 cm)	Each	19-111-022
	20 gal. (76 L)	4 ft. x 4 ft. x 4 in. (122 x 122 x 5 cm)	Each	19-111-023

Browse our full collection of safety products at fisherhealthcare.com.

Distributed by Fisher Healthcare. Contact us today:

In the United States

Order online: fisherhealthcare.com

Fax an order: 1-800-290-0290

Call customer service: 1-800-640-0640



© 2021 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at fishersci.com/trademarks.

21-535-0864 ZT 05/2021 BN20216103