

fisherbrand



Fisherbrand™ Traceable™ Three-Channel Timer

Developed with busy labs in mind

- Always ready on your benchtop with 3 channels available for tracking simultaneous timing events
- Ergonomic design provides optimal viewing angle, easy use, and increased stability on bench
- Antimicrobial protection is built in for a cleaner, more hygienic product
- Large, tactile buttons are glove-friendly
- Repetitive or recurring tasks are quick and easy with on-board memory function that returns display to previously programmed countdown time

Find it at fishersci.com and fishersci.ca

**Fisherbrand™ Traceable™
Three-Channel Timer**

The triple-display clock/timer can be used as a digital clock, timer, or stopwatch. Timer displays time of day or time remaining in any of the three timer channels. Each channel can be used either simultaneously or independently. Memory recalls previous time set. Display allows simultaneous up and down timing on different channels with unlimited time-outs. Alarm tones are unique for each channel and have adjustable volume. Flashing LCD indicates alarm condition.

In addition, timer features an antimicrobial protection which reduces the presence of odor and stain causing microbes such as bacteria, mold, and fungi on the product surface.

- Maintain compliance; includes NIST-traceable certificate from an A2LA accredited (1750.01) calibration laboratory
- Volume and buzzer timer are adjustable



Stable angled design allows easy setting and viewing without having to hold the timer

Channels	Timing capacity	Resolution	Accuracy	Count direction	Display	Item no.
3	99 hours, 59 minutes, 59 seconds	1 second	±0.001%	Up/down	Three-line LCD, 3/8"H	14-650-287

Traceable products have an individually numbered Traceable Certificate that assures accuracy from an ISO/IEC 17025:2017(1750.01) calibration laboratory accredited by A2LA. It indicates traceability of measurements to the SI units through NIST or other recognized national measurement institutes (NMI) that are signatories to the CIPM Mutual Recognition Agreement. Each product goes through an intense vetting process before it can carry the Traceable name, saving you both time and money by not having to calibrate separately.

Distributed by Fisher Scientific. Contact us today:

In the United States
Order online: fishersci.com
Call customer service: 1-800-766-7000

In Canada
Order online: fishersci.ca
Call customer service: 1-800-234-7437



fisherbrand



Fisherbrand™ Traceable™ Four-Channel Timer

Always near-at-hand with its clip-on,
magnet, and benchtop configurations

- Ergonomic design provides optimal viewing angle, easy use, and increased stability on bench
- Antimicrobial protection is built in for a cleaner, more hygienic product
- Large, tactile buttons are glove-friendly
- Maintain compliance; includes NIST-traceable certificate from an A2LA accredited (1750.01) calibration laboratory

Find it at fishersci.com and fishersci.ca

**Fisherbrand™ Traceable™
Four-Channel Timer**

This multitasking timer steps in time with four channels to time multiple events at once and default digital clock function. Each channel has a distinctive alarm that sounds for a full minute. Pressing any button will turn off the alarm. Timer memory recalls previous time set. Features time of day in 12- or 24-hour formats.

In addition, timer features an antimicrobial protection which reduces the presence of odor and stain causing microbes such as bacteria, mold, and fungi on the product surface.

- Repetitive or recurring tasks are quick and easy with on-board memory function that returns display to previously programmed countdown time
- Never miss your cue with extra-loud alarms that sound for one full minute



Set time quicker with increase and decrease buttons—no need to circle back to zero



Stable angled design allows easy setting and viewing without having to hold the timer

Channels	Timing capacity	Resolution	Accuracy	Count direction	Display	Item no.
4	99 hours, 59 minutes, 59 seconds	1 second	±0.01%	Up/down	LCD, ¾"H	14-650-288

Traceable products have an individually numbered Traceable Certificate that assures accuracy from an ISO/IEC 17025:2017(1750.01) calibration laboratory accredited by A2LA. It indicates traceability of measurements to the SI units through NIST or other recognized national measurement institutes (NMI) that are signatories to the CIPM Mutual Recognition Agreement. Each product goes through an intense vetting process before it can carry the Traceable name, saving you both time and money by not having to calibrate separately.

Distributed by Fisher Scientific. Contact us today:

In the United States
Order online: fishersci.com
Call customer service: 1-800-766-7000

In Canada
Order online: fishersci.ca
Call customer service: 1-800-234-7437

