

Get all your chemistry solutions here, on your budget.



thermo
scientific

F **fisher**
chemical

F **fisher**
bioreagents

The Fisher Scientific channel has an extensive portfolio of chemicals with the selection of grades you need for any application.

Need to stretch your lab supplies budget? Tell us what chemicals you are purchasing through other vendors and we'll provide a competitive quote for a comparable alternative.

Current product	Current price	Recommended product	Suggested price

Notes

Find it at fishersci.com and fishersci.ca

F **fisher** scientific
part of Thermo Fisher Scientific

Reach out to your Fisher Scientific Sales Representative or Thermo Scientific Chemical Account Manager to start saving on chemicals from any of the brands listed below, today!

- **Thermo Scientific** – The chemicals portfolio includes the legacy brands of Acros Organics, Alfa Aesar and Maybridge, now Thermo Scientific. It also includes a growing portfolio of chemicals optimized to work with other Thermo Scientific instruments, equipment, and consumables. We offer over 80,000 research chemicals which include a large range of organics, building blocks, inorganics, catalysts, precious metal compounds, pure elements, and drug screening compounds and libraries for drug discovery.

Also part of the portfolio is a select range of biochemicals, analytical reagents, and life science products (including high-quality buffers, substrates, enzymes, and amino acids) that go with popular Thermo Scientific instruments or life science kits and equipment.

- **Fisher Chemical** – Broad range of analytical reagents such as acids, bases, salts, standards, and titration reagents for laboratories engaged in research, development, and analysis at any level. The portfolio also consists of multiple solvent grades including high purity chromatography grades for LC/MS, and GC/MS in convenient, safe and environmentally friendly packaging.
- **Fisher Bioreagents** – Select range of products to support research in cell biology, molecular biology, and protein chemistry through an extensive, global distribution network. The Fisher Bioreagents™ brand offers chemicals that are DNase, RNase, and protease free, delivering peace of mind through quality, dependability, and convenience.

Laboratory chemicals checklist

Chromatography laboratory

- ☐ Certified ACS solvents
- ☐ Flush solutions
- ☐ GC solvents
- ☐ HPLC solvents
- ☐ Installation kits
- ☐ LC/MS solvents
- ☐ Solvent blends and additives
- ☐ UHPLC/MS solvents
- ☐ Other

Custom and bulk chemical services

- ☐ FisherPak returnable drum solvent delivery system
- ☐ Chemicals in bulk quantities
- ☐ Chemicals in custom packaging/labeling
- ☐ Custom development and synthesis services
- ☐ Custom specifications
- ☐ Global sourcing and supply chain solutions
- ☐ Other

Organic synthesis laboratory

- ☐ Acids, bases and buffers
- ☐ Amination reagents
- ☐ Base-metal catalysts and pre-catalysts
- ☐ Building blocks
- ☐ Catalyst ligands
- ☐ Drying reagents
- ☐ Extra-dry solvents
- ☐ Ferrocene derivatives
- ☐ Formylation reagents
- ☐ Grignard reagents
- ☐ Halogenation reagents
- ☐ Mitsunobu reagents
- ☐ Non-reactive laboratory essentials
- ☐ Organolithium compounds
- ☐ Organometallic halides, amines and other functional variants
- ☐ Organostannane compounds
- ☐ Organotin compounds
- ☐ Organozinc reagents
- ☐ Oxidation reagents
- ☐ Precious metal catalysts and pre-catalysts
- ☐ Reduction reagents
- ☐ Silica gel
- ☐ Solvents
- ☐ Trifluoromethylation reagents
- ☐ Other

Drug discovery laboratory

- ☐ Acids, bases and buffers
- ☐ Acrylamides
- ☐ Agaroses
- ☐ Albumins
- ☐ Aminoacids
- ☐ Antibiotics
- ☐ Antiviral compounds
- ☐ Buffers and detergents
- ☐ Building blocks
- ☐ Cell biology reagents
- ☐ Cell culture reagents
- ☐ Dyes/stains
- ☐ Functional reagents for organic synthesis
- ☐ General biochemicals
- ☐ Maybridge antiviral and antibacterial libraries
- ☐ Maybridge fragment collections
- ☐ Maybridge HitCreator library
- ☐ Maybridge HitDiscover library
- ☐ Maybridge HitFinder library
- ☐ Maybridge protein-protein interaction, g-protein coupled receptor, and kinase libraries
- ☐ Mono and poly-saccharides
- ☐ Protease and kinase inhibitors
- ☐ Solvents
- ☐ Other

Life sciences laboratory

- ☐ Acrylamides
- ☐ Agaroses
- ☐ Albumins
- ☐ Aminoacids
- ☐ Antibiotics
- ☐ Bioactive molecules
- ☐ Buffers
- ☐ Buffers and detergents
- ☐ Cell and molecular biology reagents
- ☐ Cell culture reagents
- ☐ Dyes/stains
- ☐ Gels and polymers
- ☐ General biochemicals
- ☐ Histology reagents
- ☐ Immunology reagents
- ☐ Molecular biology grade solvents
- ☐ Mono and poly-saccharides
- ☐ Pre-formulated media and broths
- ☐ Protease and kinase inhibitors
- ☐ Protein biology reagents
- ☐ Proteins and extracts
- ☐ Surfactants
- ☐ Other

Laboratory chemicals checklist continued

Applied chemistry laboratory

- ☐ Allotropic carbon forms and materials
- ☐ Anhydrous materials - ultra dry
- ☐ Catalyst ligands
- ☐ Etchants
- ☐ Fuel cell catalysts
- ☐ Inorganic compounds
- ☐ Metal catalysts and pre-catalysts
- ☐ Metals and alloys
- ☐ Nanoparticles
- ☐ Organic and inorganic acids, bases and buffers
- ☐ Photovoltaic materials

- ☐ Precious metals and complexes
- ☐ Pure elements
- ☐ Reacton™ rare-earth
- ☐ Single crystals
- ☐ Sputtering targets
- ☐ Other

Analytical laboratory

- ☐ Acids
- ☐ Analytical standards
- ☐ Bases
- ☐ Buffers
- ☐ Elemental analysis reagents
- ☐ Ion pair reagents
- ☐ Karl Fischer titration reagents
- ☐ NMR solvents
- ☐ Organic and inorganic salts
- ☐ pH testing reagents
- ☐ Standard volumetric solutions
- ☐ Other

Thermo Fisher Scientific Chemical Account Manager:

Phone number:

Email:

Customer name:

Phone number:

Email:

Fisher Scientific Sales Representative:

Phone number:

Email:

Company name:

Fisher Scientific account number:

Visit fishersci.com or fishersci.ca for full product offerings.

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Fax an order: 1-800-926-1166

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Fax an order: 1-800-463-2996

Call customer service: 1-800-234-7437

