

thermo scientific

TRANSFORM



5 Reasons to Equip Your Lab with Thermo Scientific Cold Storage Solutions

Many laboratories today are seeking improvements in the performance, reliability, and sustainability of their cold storage—and for good reasons. They want to improve efficiency and take advantage of features that support the latest technology in sample protection.

Here are 5 reasons to equip your lab with Thermo Scientific™ refrigerators, freezers, and cryogenic sample storage systems.

Scan the QR Code to Learn More





REASON 1 Selection

The Right Solution for Your Application

Thermo Scientific cold storage solutions safeguard your samples at every step, from -196°C to 5°C .



REASON 2 Performance

Protecting Your Samples and Investment

Advanced temperature control systems enable exceptional temperature stability, uniformity, and recovery backed by industry-leading warranties.



REASON 3 Sustainability

Helping You Make Greener Product Choices

Our products are ENERGY STAR™ certified, Significant New Alternatives Policy (SNAP) compliant, and My Green Lab™ ACT™ labeled.



REASON 4 Adaptability

Flexible Capacities and Configurations

Thermo Scientific cold storage solutions support a spectrum of requirements, from the smallest vials to large-scale bulk applications.



REASON 5 Productivity

Optimizing Your Workflow

Thermo Scientific products and service solutions are designed with your science in mind, helping you be confident on paper and in practice.

Explore Temperature- Controlled Support

Check out our industry-leading selection of ultra-low temperature freezers, refrigerators, cold-storage accessories, and more. Discover why we are the top choice for sample protection. Our technology safeguards your research from start to finish.

Scan the QR code to see how our cold storage solutions support your science across all temperatures.








Transform Your Lab with Greener, Smarter Solutions

Discover why Thermo Fisher Scientific is the leader in cold storage solutions. Explore a range of products through our 3D shopping experience.

Scan the QR code to see how our ultra-low freezers, refrigerators, cryogenic storage systems, and tanks enable breakthroughs with precise temperature control.








Ultra-Low Temperature Freezers

-  Tight peak variation and fast recovery
-  5-year parts and labor warranty, plus 7 additional years on compressor parts for select models
-  ENERGY STAR certified, SNAP compliant, and ACT labeled
-  Capacities ranging from 63 to 700 boxes of 2 mL vials
-  Dependability combined with storage space optimization, ergonomics, and more








High-Performance Refrigerators and Freezers

-  Variable speed control to protect products from temperature swings
-  New, standard 5-year parts and labor warranty
-  ENERGY STAR certified, SNAP compliant, and ACT labeled
-  Capacities ranging from 23 cu. ft. (650 L) to 50 cu. ft. (1,415 L)
-  Quiet, energy efficient, and easy to use and connect to monitoring systems








Undercounter Refrigerators






-  Variable speed control to protect products from temperature swings
-  Select models certified to the NSF/ANSI 456 vaccine storage standard
-  ENERGY STAR certified and SNAP compliant
-  Designed to fit tight spaces with 2°C to 8°C temperature performance
-  Built to meet the rigorous demands of healthcare, research, and industrial applications



Cryogenic Storage Systems

-  Audible alarm sounds when nitrogen level falls below safe range
-  Outstanding temperature uniformity with samples being stored below -180°C, even when less than 2 in. (5 cm) of liquid nitrogen remains in the vessel
-  Simple sample retrieval with minimal liquid nitrogen consumption
-  Compact design to optimize space with capacity for up to 6,000 samples
-  Microprocessor technology and durable construction combine precision with reliability

Autofill Cryogenic Storage Systems

-  Units available in a variety of sizes with capacities of up to 39,000 vials
-  Precise, accurate control over all parameters without complicated programming
-  Lower energy use than mechanical storage systems
-  Optional racks, canisters, frames and risers for optimum storage in the liquid or vapor phase
-  Lid with 100% clearance for minimal sample exposure and maximum safety



1 MORE REASON: **SAVINGS**

Transform Your Lab and Save



Take advantage of special offers on Thermo Scientific™ cold storage equipment.

Visit fishersci.com/cold-storage-transform or fishersci.ca/cold-storage-transform to learn more and save.

Promo No.	Description	Price
Thermo Scientific TSX Series Ultra-Low Freezers		
TSX40086APM	TSX 400-Box ULT Freezer, 115V/60Hz	\$11,888
TSX60086APM	TSX 600-Box ULT Freezer, 115V/60Hz	\$14,100
Thermo Scientific TSX Series High-Performance Undercounter Lab Refrigerator		
TSX505SAPM	TSX 5 cu. ft. Solid Door Refrigerator, 115V/60Hz	\$3,765
Thermo Scientific TSX Series High-Performance Lab Refrigerators		
TSX2305GAPM	TSX 23 cu. ft. Glass Door Refrigerator, 115V/60Hz	\$5,982
TSX2305SAPM	TSX 23 cu. ft. Solid Door Refrigerator, 115V/60Hz	\$5,870
Thermo Scientific™ Locator™ Cryogenic Storage Systems		
CY509106PM	Locator Jr Plus with Level Monitor, 2,000-Vial Capacity	\$6,452
CY509108PM	Locator 4 Plus with Level Monitor, 4,000-Vial Capacity	\$6,951
CY509109PM	Locator 6 Plus with Level Monitor, 6,000-Vial Capacity	\$7,827
CY509105PM	Locator Jr. Rack and Box System with Level Monitor, 1,600-Vial Capacity	\$6,327
CY509107PM	Locator 4 Rack and Box System with Level Monitor, 3,600-Vial Capacity	\$6,700
CY509113PM	Locator 6 Rack and Box System with Level Monitor, 6,000-Vial Capacity	\$7,827
Thermo Scientific™ CryoPlus™ Vapor Phase Starter Packages		
7400RHGBRPM	CryoPlus 1 Vapor Phase Starter Package, 90 L, 100/120V	\$12,922
7402RHGBRPM	CryoPlus 2 Vapor Phase Starter Package, 200 L, 100/120V	\$17,756
7404RHGBRPM	CryoPlus 3 Vapor Phase Starter Package, 340 L, 100/120V	\$26,069
7406RHGBRPM	CryoPlus 4 Vapor Phase Starter Package, 552 L, 100/120V	\$34,689

This promotion is open to customers in the US and Canada. The discount is taken off the list price and will apply to orders received between January 1, 2024 and March 31, 2024, or until promotional supplies are depleted, whichever comes first. No maximum purchase amount. Cannot be combined with other discounts or promotions. Offer void where prohibited, licensed, or restricted by federal, state, provincial, or local laws or regulation or agency/institutional policy. Other restrictions may apply.

U.S. customers acknowledges that this offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by customer in accordance with all federal and state laws, including without limitation the federal anti-kickback law (42 C.F.R. § 1320a-7b(b)(3)(A)) and regulations thereunder (42 C.F.R. §1001.952(h)). Other restrictions may apply.

Canada customers acknowledges that this offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by customer as applicable.

ENERGY STAR products are third-party certified by an EPA-recognized Certification Body.

MY GREEN LAB and ACT are registered and unregistered trademarks of My Green Lab, Corp., a California 501c3 non-profit corporation. All rights reserved. All other trademarks used herein are the property of their respective owners.

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

