

thermo scientific

# TRADE-UP

## 5 Reasons to Trade Up Your Cold Storage Equipment

### Transform Your Lab with Greener, Smarter Solutions

Many laboratories today are seeking improvements in the performance, reliability, sustainability, and more of their cold storage equipment—and for good reasons. They want to improve efficiency and take advantage of features that support the latest technology in sample protection.

Here are **5 reasons why** you should consider trading up to Thermo Scientific™ refrigerators, freezers, and cryogenic sample storage systems.

## REASON 1

# Selection

### The Right Solution for Your Application

Thermo Scientific cold storage solutions safeguard your samples from  $-196^{\circ}\text{C}$  to  $5^{\circ}\text{C}$ . They represent 80 years of products developed with precision, sustainability, and dependability in mind. No matter which solution you choose, you can be confident your samples will be protected from start to finish.



## REASON 2

# Performance

### Protecting Your Samples and Investment

Advanced temperature control systems enable exceptional temperature stability, uniformity, and recovery. This performance is backed by industry-leading warranties that cover virtually every aspect of your purchase for extensive time frames.



## REASON 3

# Sustainability

### Helping You Make Greener Product Choices

Our products can help you reach your environmental goals. You'll find low-GWP hydrocarbon refrigerants and greener insulation in 99% of our cold storage solutions. Our refrigerators and freezers are ENERGY STAR™ certified, Significant New Alternatives Policy (SNAP) compliant, and My Green Lab™ ACT labeled to provide clear, third-party-verified information about the environmental impact of our equipment.



## REASON 4

# Adaptability

### Flexible Capacities and Configurations

Thermo Scientific cold storage solutions support a spectrum of requirements. From the smallest vials to large-scale bulk applications, you'll find products, models, and options to support every step of your workflow.



## REASON 5

# Productivity

### Optimizing Your Workflow

Thermo Scientific products and service solutions are designed with your science in mind, helping you be confident on paper and in practice. Equip your lab today and elevate your scientific endeavors with products built to support your processes across all temperatures.



# Trade Up to Greener, Smarter Solutions

Explore a range of products that embody the **5 reasons why** you should trade up to Thermo Scientific refrigerators, freezers, and cryogenic sample storage systems.



## Ultra-Low Temperature Freezers



Tight peak variation and fast recovery



5-year parts and labor warranty, plus 7 additional years on compressor parts for select models



ENERGY STAR certified, SNAP compliant, and ACT labeled



Capacities ranging from 63 to 700 boxes of 2 mL vials



Dependability combined with storage space optimization, ergonomics, and more



## High-Performance Refrigerators and Freezers



Variable speed control to protect products from temperature swings



New, standard 5-year parts and labor warranty



ENERGY STAR certified, SNAP compliant, and ACT labeled



Capacities ranging from 23 cu. ft. (650 L) to 50 cu. ft. (1,415 L)



Quiet, energy efficient, and easy to use and connect to monitoring systems



## Undercounter Refrigerators



Variable speed control to protect products from temperature swings



Select models certified to the NSF/ANSI 456 vaccine storage standard



ENERGY STAR certified and SNAP compliant



Designed to fit tight spaces, including a model with 2°C to 8°C temperature range and 50 cu. ft. (1,415 L) capacity



Built to meet the rigorous demands of healthcare, research, and industrial applications



## Cryogenic Storage Systems



Audible alarm sounds when nitrogen level falls below safe range



Precise, accurate control over all parameters without complicated programming



Simple sample retrieval with minimal liquid nitrogen consumption



Compact design to optimize space with capacity for up to 6,000 samples



Microprocessor technology and durable construction combine precision with reliability

## Controlled-Rate Freezers



Precise, repeatable freezing results to protect samples



Designed to support 21 CFR part 11 and GMP needs



Intuitive touchscreen display for easy setup, operation, and freezing run review



USB data export of PDF run logs and support for OPC-UA serial communication protocol



User-friendly operation, enhanced data traceability, and high throughput capability



## Trade Up and Save



Take advantage of special offers on Thermo Scientific™ cold storage equipment. Visit [fishersci.com/cold-storage-trade](https://fishersci.com/cold-storage-trade) or [fishersci.ca/cold-storage-trade](https://fishersci.ca/cold-storage-trade) to learn more and save.

Mfr. No.	Promo No.	Description	Price
<b>Thermo Scientific TSX Series Ultra-Low Temperature Freezers</b>			
TSX50086ATI	TSX50086ATI	TSX 500-Box ULT Freezer, 115V/60Hz	\$13,400
TSX50086DTI	TSX50086DTI	TSX 500-Box ULT Freezer, 208-230V/60Hz	\$13,400
TSX60086ATI	TSX60086APM	TSX 600-Box ULT Freezer, 115V/60Hz	\$14,100
TSX60086DTI	TSX60086DPM	TSX 600-Box ULT Freezer, 208-230V/60Hz	\$14,100
TSX70086ATI	TSX70086APM	TSX 700-Box ULT Freezer, 115V/60Hz	\$15,100
TSX70086DTI	TSX70086DPM	TSX 700-Box ULT Freezer, 208-230V/60Hz	\$15,100
<b>Thermo Scientific TSX Series High-Performance Lab Freezer</b>			
TSX2320FARP	TSX2320FARP	TSX 23 cu. ft. -20°C Manual Defrost Freezer, 120V/60Hz	\$5,990
<b>Thermo Scientific TSX Series High-Performance Lab Refrigerators</b>			
TSX2305GARP	TSX2305GARP	TSX 23 cu. ft. Glass Door Refrigerator, 120V/60Hz	\$5,865
TSX2305SARP	TSX2305SARP	TSX 23 cu. ft. Solid Door Refrigerator, 120V/60Hz	\$5,755
TSX5005GARP	TSX5005GAPM	TSX 50 cu. ft. Glass Door Refrigerator, 120V/60Hz	\$7,890
TSX505SARP	TSX505SAPMO	TSX 5 cu. ft. Solid Door Refrigerator, 115V/60Hz	\$3,691
<b>Thermo Scientific TDE Series Ultra-Low Temperature Chest Freezers</b>			
TDEC06386FAU	13-762-409PM	TDE 3 cu. ft. ULT Chest Freezer, 115V/60Hz	\$7,000
TDEC39686FAU	13-762-415PM	TDE 20 cu. ft. ULT Chest Freezer, 115V/60Hz	\$12,000
<b>Thermo Scientific™ CryoMed™ Controlled-Rate Freezers</b>			
TSCM17FATI	TSCM17FAPM	CryoMed 17 L General Purpose Freezers with OPC UA	\$42,827
TSCM34FATI	TSCM34FAPM	CryoMed 34 L General Purpose Freezers with OPC UA	\$44,827
TSCM48FATI	TSCM48FAPM	CryoMed 48 L General Purpose Freezers with OPC UA	\$46,643
<b>Thermo Scientific™ Locator™ Plus Cryogenic Storage Systems</b>			
CY509106-BOGO50	13-762-353PM	Two Locator Jr. Plus Rack and Box Systems with Level Monitor	\$12,903
CY509108-BOGO50	13-762-355PM	Two Locator 4 Plus Rack and Box Systems with Level Monitor	\$13,902
CY509109-BOGO50	13-762-356PM	Two Locator 6 Plus Rack and Box Systems with Level Monitor	\$15,654
CY509106CART	13-762-353CRT*	Locator Jr. Plus System with Level Monitor and Wheeled Accessory Cart	\$8,602
CY509108CART	13-762-355CRT*	Locator 4 Plus System with Level Monitor and Wheeled Accessory Cart	\$9,268
CY509109CART	13-762-356CRT*	Locator 6 Plus System with Level Monitor and Wheeled Accessory Cart	\$10,436

Discounts taken off list price. Prices shown reflect promotional prices. Offer valid through December 31, 2023. U.S. customers acknowledge that this offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by customer in accordance with all federal and state laws, including without limitation the federal anti-kickback law (42 U.S.C. § 1320a-7b(b)(3)(A)) and regulations thereunder (42 C.F.R. §1001.952(h)). Canada customers acknowledge that this offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by customer as applicable. \*Excludes U.S. healthcare customers.

Distributed by Fisher Scientific. Contact us today:

**In the United States**

Order online: [fishersci.com](https://fishersci.com)

Call customer service: 1-800-766-7000

**In Canada**

Order online: [fishersci.ca](https://fishersci.ca)

Call customer service: 1-800-234-7437